



# 3M™ Quat Disinfectant Cleaner *(Ready to use)*

## Product Details

- EPA registered quaternary disinfectant cleaner for use in hospitals
- Effective against HIV-1, MRSA, VRE, herpes simplex I and II and other pathogens
- Inhibits the growth of mold and mildew, and their odors, when used as directed.
- Proven “one-step” disinfectant / cleaner
- Rinse-free in one labour-saving step
- Has a pleasant fragrance
- Volumes Available: 650ml (Most Popular), 4 Litre, 20 Litre

**Applications:** Most washable surfaces, including windows, glass, mirrors, carpets, floors and walls

❖ **Easy to use** ❖ **Clean and Safe environment** ❖ **Less frequent disinfecting** ❖ **Cost Savings**



## Test Result

	Before Cleaning	After Cleaning
Floor	1397 RLU	103 RLU ↓
Door	339 RLU	140 RLU ↓

\* Relative Light Unit (RLU) is a unit for measuring cleanliness by measuring the levels of Adenosine Triphosphate.

- ❖ The door is applied with Quat Disinfectant Cleaner using mist spray or blower machine and then air-dried (Treated surfaces can be wipe dry with a cloth, sponge, mop or allow to air dry)
- ❖ A Walk - Behind Scrubber and Dryer machine is used to disperse Quat Disinfectant Cleaner and then scrub and dry the floor.



**Lim Kim Hai Electric Co (S) Pte Ltd**  
Lim Kim Hai Building,  
53 Kallang Place, Singapore  
339177

[www.limkimhai.com.sg](http://www.limkimhai.com.sg)

Contact us today at [solutions@limkimhai.com.sg](mailto:solutions@limkimhai.com.sg)

Hotline: +65 6490 5000